



1a

fmGenie



Connecting an fmGenie to external equipment

The Aux input on an fmGenie transmitter can be plugged directly into a TV or video SCART socket or similar signal level. A transmitter input adaptor is available for connecting to other equipment.



Stereo 3.5mm to phono lead

5 metre lead which, when used with a ★T114★, will connect between a TV or video scart socket and the 'Aux in' on an fmGenie transmitter.



★A121BA★

Qty 1-19 £ 2.53 each

Qty 20+ £ 0.72 each



Inline SCART to phono splitter

This adaptor can be used to take sound from your TV system.

★T114H★

Qty 1-19 £ 3.24 each

Qty 20+ £ 1.67 each



See section 11 for a SCART socket doubler, part no. ★T113Z★

fmGenie transmitter stereo input adaptor

The transmitter input adaptor has its own volume control and plugs into the transmitter 'Ext mic' socket. Order pack of leads separately – either choose our general pack of leads shown on the right or use your own connecting lead.



FMG81 £ 19.90 each



Pack of stereo leads (For items FMG81 or 2206S)

This pack will allow connection to a wide range of electronic equipment.

To fit stereo 3.5mm, 6.3mm, phono & 5 pin DIN sockets – including 3.5mm doubler.

If you are connecting to a mono device simply leave one of the ends loose.

FMG81PK

£ 9.00 each



fmGenie rebroadcast soundfield connection pack

Attenuated connection lead to connect the aux o/p of a soundfield system to an fmGenie microphone input socket. Includes phono to 2.5mm jack plug lead & wall hook.

45SIBKFMG £ 9.50 each



fmGenie telephone listening adaptor

This useful little gizzmo is connected in the curly cord lead between the telephone handset and the base unit. The 2.5mm jack then plugs into the fmGenie microphone socket – Tx or Rx.

FMG9PK04B £ 35.00 each



Using an fmGenie to listen to an office telephone

You can use your fmGenie to listen directly to your corded telephone – in our experience this will give you the best quality sound of any method we have tried.

There are two options, one via the curly cord of a telephone handset (pt no FMG9PK04B above) and this one for use with a handsfree headset in a work situation such as telesales.

An accessory pack including a headset & base station are on page 32.



Conventional telephone headset connection

Plantronics SupraPlus headset to fmGenie adaptor

Using an fmGenie to listen to the telephone provides the ultimate in office telephone listening.

This Y adaptor allows the direct connection of an fmGenie to a Plantronics telephone headset system.

Y Lead lengths approx. 2metre overall with 200mm feed & 180mm lead to fmGenie. The Y lead has a standard Plantronics headset plug & socket with a 2.5mm plug for connection to the fmGenie microphone input.

FMG81SUP £ 39.95 each



You can also visit www.connevans.com/fmgenie and download our information sheets on connecting to telephones at home or at work.

